

NEXUS Nitrogen Generator Range The latest in high performance Nitrogen generation

PCL's brand new range of Nitrogen products branded 'NEXUS' – meaning 'the most central and most important point' combines PCL's ethos of designing and manufacturing marketing leading Nitrogen generation equipment in a modern, innovative and simple to use housing.

The PCL NEXUS series generators allow the operator to use existing equipment to deliver high purity Nitrogen to the desired application.

Key Product Benefits

- Revenue generation for Service Providers.
- Cost effective Nitrogen delivery with very low maintenance.
- Low life time costs with high grade filtration and high performance components.
- Guaranteed tank pressure accuracy and robustness.

www.pclairtechnology.com





Key Product Features

- Mobile to allow efficient and flexible positioning and usage.
- Nitrogen purity check point.
- Internal tanks meet EEC standards.
- Easy to operate and quick installation.
- Digital adjustable tank set pressure control.

Technical Specifications

Dimensions (cabinet only):

Height: 1364mm Width: 600mm Depth: 470mm

Weight:

NEX2G: 153kg NEX6G: 246kg NEXMG: 128kg

Temperature Range

Operating: 0°c to 40°c Storage: -40°c to 70°c

Pressure Measurement

Accuracy: To +/- 0.5% of full scale reading

(Exceeds EC Directive 86/217)

Tank Reading Accuracy: 0.1bar/1psi/10kPa

Electrical Interface

Voltage (nominal): 230-240Vac Current Typical (idle): 8VA

Max: 12VA

Cable length: 2.5m

Tyre Operating Performance

NEX2 Operating PerformancePSA - 2 X CMS Towers
890 x 159mm

NEX2 Generator (*minimum compressor flow required)

Nitrogen Flow @ 10 bar supply 95%+ purity

70 l/min (2.5 cfm) (*368 l/min)

NEX6 Operating Performance NEX6 Generator
(*minimum compressor flow required)

PSA - 4 X CMS Towers 890 x 159mm

200 l/min (7.0 cfm) (*538 l/min)

supply 95%+ purity

NEXM Operating

Nitrogen Flow @ 12 bar

NEXM Generator

PerformanceParker Membrane
TS OEM Kit 30

(*minimum compressor flow required)

Nitrogen Flow @ 10 bar supply 95%+ purity

484 l/min (17.1 cfm) (*1269 l/min)

Nitrogen Flow @ 12 bar supply 95%+ purity

580 l/min (20.5 cfm) (*1523 l/min)

Nitrogen Flow @ 10 bar supply 97%+ purity

309 l/min (10.9 cfm) (*1066 l/min)

Nitrogen Flow @ 12 bar supply 97%+ purity

371 l/min (13.1 cfm) (*1279 l/min)

| Series | Description | Application |
|--------|----------------------------------|-------------|
| NEX2G | NEXUS N2 Generator only | |
| NEX6G | NEXUS N6 Generator only | |
| NEXMG | NEXUS Membrane Generator only | |